

183039-1 Product Details

Have a Question?

Chat with a Product Information Specialist



183039-1

TE Internal Number: 183039-1

Active

[View 3D PDF](#)

CPC (Circular Plastic) and Circular Metal-Shell Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Not Preloaded
- 14 Positions
- 14 Signal Positions
- 0 Power Positions
- Connector Style = Plug

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [C.P.C. plug ass'y std. sex size 17-14](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B1)
- [3D Model](#) (IGES, Version B1)
- [3D Model](#) (STEP, Version B1)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Contact Arrangement](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Mount](#) = Free Hanging
- [Mount Angle](#) = Straight
- [Shell Size](#) = 17
- [Shell Type](#) = All Plastic
- [Product Series](#) = Series 1
- [Thread Size](#) = 15/16-20 UNEF-2A
- [Sealed](#) = No
- [Mating Polarization Type](#) = Keyed

Mechanical Attachment:

- [Number of Power Positions](#) = 0
- [Mating Retention Type](#) = Threaded Coupling
- [VDE Tested](#) = No

Body Related Features:

- [Number of Positions](#) = 14
- [Number of Signal Positions](#) = 14
- [Fluid Resistance](#) = None

Contact Related Features:

- [Preloaded](#) = No
- [Accepts Contact Gender](#) = Socket
- [Standard or Reverse Gender](#) = Standard

Housing Related Features:

- [Connector Style](#) = Plug
- [Housing Material](#) = Thermoplastic - GF
- [Housing Color](#) = Black
- [UL Flammability Rating](#) = UL 94V-0

Configuration Related Features:

- [Environmental Protection](#) = Without
- [Reverse Numbering](#) = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [UL Rating](#) = Recognized
- [CSA Certified](#) = Yes

Other:

- [Brand](#) = AMP

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

