



## 5106015-1 Product Details

### Have a Question?

Chat with a Product Information Specialist



**5106015-1**

TE Internal Number: 5106015-1

Active

[View 3D PDF](#)

### 2mm Hard Metric PCB Mount Connectors (Z-PACK 2mm HM)

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

#### Product Highlights:

- Connector
- Housing Gender = Receptacle
- Contact Gender = Pin
- Type = Type A
- Interface Type = 2mm HM

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- [Z-PACK 2mm HM TYPE A 110 POS. RIGHT ANGLE MALE CONNE...](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- None Available

##### Application Specifications:

- [Z-PACK 2mm HM Interconnection System for Board-to-Bo...](#) (PDF, English)

##### Instruction Sheets:

- None Available

##### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

##### Additional Information:

- [Product Line Information](#)

##### Related Products:

- [Tooling](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Product Type = Connector
- [PCB Mount Angle](#) = Right Angle
- [Mating Polarization](#) = With
- [Mating Polarization Type](#) = Multi-Purpose Center
- Comment = Connector conforms to all testing according to IEC 61076-4-101, Performance Level 2.

##### Mechanical Attachment:

- [Board Mount](#) = Free Board
- [Module Length \(mm \[in\]\)](#) = 50.00 [1.968]
- [Crosstalk Version](#) = Standard
- AMP Standard Option Number = 1

##### Electrical Characteristics:

- [Shielded](#) = No

##### Termination Related Features:

- [Interface Type](#) = 2mm HM
- Termination End Plating = Tin over Nickel

##### Body Related Features:

- [Type](#) = Type A
- [Number of Rows](#) = 5
- [Number of Positions](#) = 110
- [Grounding Contact](#) = Without
- Rows Loaded = A, B, C, D, E

##### Contact Related Features:

- Contact Gender = Pin
- [Contact Type](#) = Signal
- [Feedthrough Post Length \(mm \[in\]\)](#) = 3.71 [0.146]
- [CompactPCI](#) = Yes
- [Contact Plating, Mating Area, Material](#) = Gold (50)
- Contact Style = Short Tail
- Contact Base Material = Phosphor Bronze

##### Housing Related Features:

- Housing Gender = Receptacle
- Housing Material = Polyester GF
- Housing Color = Gray
- UL Flammability Rating = UL 94V-0

##### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

##### Packaging Related Features:

- Packaging Quantity = 11

##### Other:

- Brand = Tyco Electronics

BOOKMARK ...

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

Follow us on: