

## 5747830-4 Product Details

### Have a Question?

Chat with a Product Information Specialist



**5747830-4**

TE Internal Number: 5747830-4

**Active**

### Standard Board Mount Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- 25 Positions
- Housing Gender = Receptacle
- PCB Mount Angle = Right Angle
- Product Series = HD 20
- With Mating Connector Lock

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(9\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)
- [Mating Products \(9\)](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [PCB Mount Angle](#) = Right Angle
- [Product Series](#) = HD 20
- [Mating Connector Lock](#) = With
- [Mating Connector Lock Type](#) = Threaded Inserts
- [PCB Mount Retention](#) = With
- [Shell Type](#) = Front Metal Shell
- [Shell Size](#) = 3
- [Footprint \(mm \[in\]\)](#) = 14.99 [.590]
- [Grounding Indents](#) = Without
- [Grounding Straps](#) = With
- [PCB Mount Style](#) = Through Hole
- [Color Code](#) = None
- Sealed = No
- Profile = Standard
- Post Size (mm [in]) = 0.66 [.026]
- Mounting Hole Diameter (mm [in]) = 3.18 [.125]
- Shell Material = Steel
- Threaded Insert Material = Zinc
- Eyelet Material = Brass

#### Mechanical Attachment:

- [Panel Attachment](#) = Without
- Boardlock Material = Copper Alloy
- Boardlock Plating = Tin

#### Termination Related Features:

- [Grounding Clips](#) = Without
- [Termination Post Length \(mm \[in\]\)](#) = 3.18 [0.125]
- [Solder Tail Contact Plating](#) = Tin over Nickel

#### Body Related Features:

- [Number of Positions](#) = 25
- [PCB Mount Retention Type](#) = Boardlock(s)
- Shell Plating = Tin
- Threaded Insert Plating = Clear Chromate
- Eyelet Plating = Tin

#### Contact Related Features:

- [Contact Plating, Mating Area, Material](#) = Gold (30)
- Contact Shape = Round
- Contact Base Material = Phosphor Bronze

#### Housing Related Features:

- Housing Gender = Receptacle
- UL Flammability Rating = UL 94V-0
- Housing Material = Thermoplastic - GF

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [PCB Thickness, Recommended \(in \[mm\]\)](#) = 0.062 [1.57]

#### Operation/Application:

- Application = Standard

#### Other:

- Brand = AMP

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

Follow us on: