

180464-5 Product Details



180464-5

TE Internal Number: 180464-5

Active

[View 3D PDF](#)

FASTON Uninsulated Receptacles & Housings

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.81 mm
- Board Mount = No
- Receptacle Style = Flag

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [FASTON conn. .250 sr. flag rec. etc.](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Blocchetto di protezione per capicorda lamellari fem...](#) (PDF, Italian)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version AW5)
- [3D Model](#) (IGES, Version AW5)
- [3D Model](#) (STEP, Version AW5)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions (mm [in]) = 6.35 x 0.81 [.250 x .032]
- Receptacle Style = Flag
- Insulation Support = Insulation Support
- Wire/Cable Type = Stranded
- Insulation Diameter (mm [in]) = 2.49-3.81 [.098-.150]
- Insertion Force = Normal
- Material = Phosphor Bronze
- Finish = Tin
- Crimp Type = F-Crimp

Mechanical Attachment:

- Board Mount = No

Body Features:

- Weld Tab = Without
- Wire Range (mm [AWG]) = 1.00-2.50² [17-13]

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Features:

- Packaging Method = Strip
- Packaging Quantity = 7,000

Other:

- For Hermetic Header Tab = No
- Line = Premier
- Brand = AMP
- Comment = For mini tooling.; Reverse Reel

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

