



Search bar: What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Resistors > Product Feature Selector > Product Details

RP73D1J732RBTGDG Product Details

Share | Print | Email



RP73D1J732RBTGDG
(1-1879745-3)

TE Internal Number: 1-1879745-3

Active

Fixed Resistors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Fixed Resistor
- Resistor Type = Precision Resistor
- Resistance Selection = <1K Ω
- Resistance = 732 Ω
- Power Rating = .10 W

[View all Features](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [1309350_PASSIVE_COMPONENT](#) (PDF, English)
- [SMD Precision Resistors - Type RP73 Series - Tyco El...](#) (PDF, English)
- [8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Fixed Resistor
- Resistor Type = Precision Resistor
- Element = Thin Film
- Series = RP73
- Termination Type = Solder

Electrical Characteristics:

- Resistance Selection (Ω) = <1K
- Resistance (Ω) = 732
- Power Rating (W) = 0.10
- Tolerance (%) = 0.1

Body Features:

- Mount Style = Surface Mount
- Packaging Style = 0603
- Package, Component Size = 1.6 x 0.8

Configuration Features:

- Number of Terminations = 2
- Number of Resistors = 1

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = ± 15

Operation/Application:

- [Application](#) = Precision

Packaging Features:

- [Package Type](#) = Taped and Reeled

Other:

- [Brand](#) = Holsworthy

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

