MRJE2604 Product Details



<u>Active</u>

Rotary Switches

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Number of Positions = 6
- Angle of Throw = 30.00 °
- Actuator Style = Long Thin Knob
- Code Type = 2 Poles
- Straight Mount Angle

View all Features

Quick Links

- Check Pricing & Availability
 - Search for Tooling
- Product Feature Selector
 Contact Us About This Product

Documentation & Additional Information

Product Drawings:

■ MINIATURE ROTARY SWITCH 12 POS.-30 DEGREE DETENT (PDF, English)

Catalog Pages/Data Sheets:

None Available

Product Specifications:

None Available

Application Specifications:

None Available

Instruction Sheets:

None Available

CAD Files:

None Available

Additional Information:

Product Line Information

Related Products:

Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Number of Positions = 6
- Angle of Throw (°) = 30.00
- Actuator Style = Long Thin Knob
- <u>Code Type</u> = 2 Poles
- Mount Angle = Straight
- Product Series = MRJE
- Comment = Process Sealed Splash proof; Fixed

Electrical Characteristics:

Contact Rating = 0.4VA

Termination Related Features:

Solder Tail Contact Plating = Gold over Nickel

Contact Related Features:

Contact Material = Brass

Housing Related Features:

Housing Material = Die Cast Zinc

Industry Standards:

List all Documents

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- <u>Lead Free Solder Processes</u> = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

• Brand = Alcoswitch

Languages: English | Deutsch | Español | Português (do Brasil) | Русский | Italiano | 正體中文 (繁體) | 中文 (简体) | 日本語 Country Sites: China | Japan

Provide Website Feedback | Contact Customer Support

Home | Customer Support. | Supplier. | Site Map. | Privacy Policy. | Browser Support. © 2007 Tyco Electronics Corporation All Rights Reserved