

Housings

Description	Part No.	Width	Length	Height
① HB.16.STS-GR.1.21G	1-1102292-7	43.0	93.5	60.0
② HB.16.STD-GR.1.21G	1-1102295-7	43.0	93.5	60.0
③ HB.16.AG-LB	1-1102296-2	43.5	113.0	28.5
④ HB.16.AGD*-LB	1-1102305-2	43.5	113.0	28.5
⑤ HB.16.SG-LB.1.21Z	1-1102299-2	57.0	117.0	55.5
⑥ HB.16.SGD*-LB.1.21Z	1-1102308-2	57.0	117.0	55.5
⑦ HB.16.KDO-LB.1.21G	1-1102304-2	43.0	73.0	55.5

① HD.40.STS-GR.1.29G	1-1102567-7**	43.0	93.5	76.0
② HD.40.STD-GR.1.29G	1-1102570-7**	43.0	93.5	76.0
③ HD.40.SG-LB.1.29Z	1-1102579-2**	57.0	117.0	76.5
④ HD.40.SGD*-LB.1.29Z	1-1102593-2**	57.0	117.0	76.5
⑤ HD.40.KDO-LB.1.29G	1-1102587-2**	43.0	93.5	79.5

⑥ HB.16.STS.1.21G	1-1102292-6	43.0	93.5	60.0
⑦ HB.16.STD.1.21G	1-1102295-6	43.0	93.5	60.0
⑧ HB.16.AG-VS	1-1102296-1	57.0	113.0	28.5
⑨ HB.16.SG-VS.1.21Z	1-1102299-1	57.0	117.0	55.5
⑩ HB.16.KDO-VS.1.21G	1-1102304-1	57.0	93.5	65.5

⑥ HD.40.STS.1.29G	1-1102567-6**	43.0	93.5	76.0
⑦ HD.40.STD.1.29G	1-1102573-6**	43.0	93.5	76.0
⑨ HD.40.SG-VS.1.29Z	1-1102579-1**	57.0	117.0	76.5
⑩ HD.40.KDO-VS.1.29G	1-1102587-1**	57.0	93.5	79.5

① HB.24.STS-GR.1.21G	1-1102316-7	43.0	120.0	70.0
② HB.24.STD-GR.1.21G	1-1102325-7	43.0	120.0	70.0
③ HB.24.AG-LB	1-1102291-2	43.5	140.0	28.5
④ HB.24.AGD*-LB	1-1102340-2	43.5	140.0	28.5
⑤ HB.24.SG-LB.1.21Z	1-1102331-2	57.0	144.0	55.5
⑥ HB.24.SGD*-LB.1.21Z	1-1102343-2	57.0	144.0	55.5
⑦ HB.24.KDO-LB.1.21G	1-1102336-2	43.0	120.0	55.5

① HD.64.STS-GR.1.29G	1-1103338-7**	43.0	120.0	78.0
② HD.64.STD-GR.1.29G	1-1103344-7**	43.0	120.0	78.0
③ HD.64.SG-LB.1.29Z	1-1103350-2**	57.0	144.0	78.5
④ HD.64.SGD*-LB.1.29Z	1-1103364-2**	57.0	144.0	78.5
⑤ HD.64.KDO-LB.1.29G	1-1103358-2**	42.75	120.0	81.5

⑥ HB.24.STS.1.21G	1-1102316-6	43.0	120.0	70.0
⑦ HB.24.STD.1.21G	1-1102325-6	43.0	120.0	70.0
⑧ HB.24.AG-VS	1-1102291-1	57.0	140.0	28.5
⑨ HB.24.SG-VS.1.21Z	1-1102331-1	57.0	144.0	55.5
⑩ HB.24.KDO-VS.1.21G	1-1102336-1	57.0	120.0	57.0

⑥ HD.64.STS.1.29G	1-1103338-6**	43.0	120.0	78.0
⑦ HD.64.STD.1.29G	1-1103344-6**	43.0	120.0	78.0
⑨ HD.64.SG-VS.1.29Z	1-1103350-1**	57.0	120.0	78.5
⑩ HD.64.KDO-VS.1.29G	1-1103358-1**	57.0	120.0	81.5

*AGD/*SGD Surface mounted-/socket housing with lid

**High Construction

Material: Aluminum die-cast alloy

Protection Class: IP 65

Contact Inserts

Description	Part No.	Screw	Crimp	Spring Clamp
④ HE.16.Sti.S	1-1103638-1	●		
HE.16.Bu.S	1-1103639-1	●		
HE.16.Sti.C	2-1103638-3		●	
HE.16.Bu.C	2-1103639-3		●	
HE.16.Sti.SC	7-1103638-1			●
HE.16.Bu.SC	7-1103639-1			●
⑥ HN.D.40.Sti.C	2-1103110-3		●	
HN.D.40.Bu.C	2-1103111-3		●	
⑦ HN.2D.7Z.Sti.C	2-1103208-3		●	
HN.2D.7Z.Bu.C	2-1103212-3		●	
⑩ HSB.5/35.Sti.S	1-1104204-1	●		
HSB.5/35.Bu.S	1-1104205-1	●		

④ HE.24.Sti.S	1-1103640-1	●		
HE.24.Bu.S	1-1103641-1	●		
HE.24.Sti.C	2-1103640-3		●	
HE.24.Bu.C	2-1103641-3		●	
HE.24.Sti.SC	7-1103640-1			●
HE.24.Bu.SC	7-1103641-1			●
⑥ HN.D.64.Sti.C	2-1103112-3		●	
HN.D.64.Bu.C	2-1103113-3		●	
⑦ HN.2D.108.Sti.C	2-1103216-3		●	
HN.2D.108.Bu.C	2-1103220-3		●	

Material: Polycarbonate

Crimp contacts: please see HA/HE & HN.D