


Mounting Clips


Panel cut-out dimensions are for reference only, see current AMP customer drawing for details.

For Econoseal J Series Mark II- Connectors . . . Type 1




Part Number	Material and Color	Panel Thickness
85000-1	Nylon, Black	0.7-1.6 [0.028-0.063]

Panel Cut-Out Dimensions



For Econoseal J Series Mark II- Connectors . . . Type 2




Part Number	Material and Color	Panel Thickness
626897-1	Nylon, Natural	0.56-5.10 [.022-.201]

Panel Cut-Out Dimensions



For Econoseal III, .250 Series Wire To Wire Connectors



Part Number	Material and Color	Panel Thickness
345485-1	Nylon, Black	0.8-1.6 [.031-.063]

Panel Cut-Out Dimensions



For .187 Series Sealed Connectors



Part Number	Material and Color	Panel Thickness
85003-2	Nylon, Black	2.5 [.098]

Panel Cut-Out Dimensions

