

Crimp and Split-Ring Ferrules (Continued)

Shell Size	Cable Dia. (Max.)	When using these Shield Kits				Use these Ferrules				
		Straight Exit Shield Kit No.		90° Exit Die Cast Shield Kit No.		Split-Ring* Ferrule No.	Crimp Ferrule No. and Tooling No.**			
		Die Cast	Metal-Plated Plastic	With Slide Latch	Without Slide Latch		Inner	Outer	Die Set for Hand Tool 54334-1	Applicator Die Set
4	.240 6.10	745174-4	747100-7	—	—	—	2-745129-1	745130-8	543013-3	813809-1
	.280 7.11	745174-4	747100-7	—	—	—	3-745129-2	1-745130-6	1-543013-6	813809-7
	.350 8.90	745174-5	747100-9	—	—	745508-5	—	—	—	—
	.350 8.90	745174-4	747100-7	—	—	—	2-745129-0	745130-9	543013-4	813809-2
	.430 10.92	745174-4	747100-7	—	—	745508-1	1-745129-9	1-745130-1	543013-7	813809-3
	.500 12.70	745174-3	747100-5	—	—	745508-8	—	—	—	—
	.525 13.34	745174-1	747100-1	—	—	—	2-745129-6	1-745130-2	1-543013-1	813809-4
	.575 14.61	745174-2	747100-3	—	—	1-745508-0	—	—	—	—
	.650 16.51	745174-1	747100-1	—	—	1-745508-1	—	—	—	—
	5	.240 6.10	745175-6	—	—	—	—	1-745129-8	745130-8	543013-2
.365 9.27		745175-6	—	—	—	—	1-745129-7	1-745130-0	543013-6	813809-5
.375 9.53		745175-6	—	—	—	745508-6	—	—	—	—
.430 10.92		745175-4	—	—	—	—	2-745129-3	1-745130-1	543013-8	813809-3
.450 11.43		745175-5	—	—	—	745508-7	—	—	—	—
.525 13.34		745175-4	—	—	—	745508-9	—	—	—	—
.530 13.46		745175-4	—	—	—	—	2-745129-2	1-745130-2	1-543013-0	813809-4
.600 15.24		745175-3	—	—	—	1-745508-0	—	—	—	—
.650 16.51		745175-1	747098-1	—	—	—	2-745129-9	1-745130-3	1-543013-4	813809-6
.675 17.15		745175-2	—	—	—	1-745508-1	—	—	—	—
.750 19.05	745175-1	747098-1	—	—	1-745508-2	—	—	—	—	

*For split-ring ferrules, Min. O.D. is .040 [1.02] smaller than Max. O.D.

**For inner and outer ferrules, Min. O.D. is .050 [1.27] smaller than Max. O.D. At the Max. cable O.D. the Min. insulation thickness is .060 [1.52].

Note: Refer to page 148 for Application Tooling for ferrules.

Cable Connectors