

BNC Connectors, 50 Ohm (Continued)

Plugs, Crimp (Continued)

Connector Cable Range Selection Code ¹	RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	M39012/Military No. and/or Comments	Part No.	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 678304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1
C1	180, 180A, 180G, 195, 195A	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	2-221128-5	1.320 33.53	—	58436-3	—
		Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	225395-9	1.395 35.42	69477-2	—	69669-2
		Dual Crimp	Tin Lead	Nickel	Polyethylene	Commercial	—	3-227079-7	1.090 27.69	69477-4	58539-1	—
		Dual Crimp	Gold	Silver	TEFLON	Mil Type	—	2-331350-6	1.395 35.44	69477-2	—	69669-2
		Single Crimp	Gold	Silver	TEFLON	Mil Type	—	2-329447-1	1.312 33.33	69246-1	—	69423
C2	Belden 8219	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	2-221128-7	1.320 33.53	—	58436-1	—
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	6-227079-7	1.090 27.69	220187-1	58435-1	220217-1
	Belden 9907, 89907 Comm/Scope 2104	Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	6-227079-8	1.090 27.69	220187-1	3-8452-2	220217-1
C3	Belden 8218	Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	1-225395-0	1.188 30.18	69477-2	—	69669-2
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	1-227079-9	1.090 27.69	69477-4	58539-1	58376-1
		Dual Crimp	Tin Lead	Nickel	Polyethylene	Commercial	—	1-227079-7	1.090 27.69	69477-4	58539-1	58376-1
		Dual Crimp	Gold	Silver	TEFLON	Mil Type	—	2-331350-2	1.188 30.18	69477-2	—	69669-2
D	58, 58A, 58B, 58C	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	Bulk Packaged	221128-1	1.320 33.53	—	58436-1	—
		Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	1-221128-0	1.320 33.53	—	58436-1	—
		Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	225395-1	1.328 33.74	69478-1	220189-3	69727
		Dual Crimp	Tin Lead	Nickel	Polyethylene	Commercial	—	227079-1	1.090 27.69	220187-1	220189-1	220217-1
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	227079-5	1.090 27.69	220187-1	58435-1	220217-1
		Dual Crimp	Silver	Nickel	Polyethylene	Commercial	—	227079-9	1.090 27.69	220187-1	58435-1	220217-1
		Dual Crimp	Gold	Silver	TEFLON	Mil Type	16E0004	2-331350-1	1.328 33.74	69478-1	220189-3	69727
		Single Crimp	Gold	Silver	Polypropylene	Mil Type	—	2-329082-1	1.312 33.33	69140-1	—	69223-1
		Single Crimp	Gold	Silver	TEFLON	Mil Type	—	2-329444-1	1.312 33.33	69140-1	—	69223-1
		Single Crimp	Gold	Silver	TEFLON	Mil Type	Weatherproof	330884	1.546 39.27	69376-3	—	69615
D1	141, 141A, 303	Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	225395-5	1.188 30.13	69478-1	220189-3	69727
		Single Crimp	Gold	Silver	TEFLON	Mil Type	—	2-330358-1	1.312 33.33	69140-1	—	—
D2	Belden 88240, Berk-Tek BTDC-5E, Comm/Scope 2135	Hex Crimp	Gold	Nickel	Polyethylene	Commercial	—	1-221128-0	1.320 33.53	—	58436-1	—
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	4-227079-3	1.312 33.33	220187-1	58435-1	220217-1
		Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	4-225395-2	1.312 33.33	69478-1	220189-3	69727
E	223, 55, 55A, 55B	Dual Crimp	Gold	Nickel	TEFLON	Mil Type	—	225395-3	1.718 43.64	69478-1	220189-3	69727
		Dual Crimp	Gold	Nickel	Polyethylene	Commercial	—	227079-6	1.280 27.69	220187-1	58435-1	220217-1
		Single Crimp	Gold	Silver	TEFLON	Mil Type	—	2-329444-2	1.312 33.33	69140-2	—	69424

¹Refer to page 14 for code specifications.

²Order AMP PRO-CRIMPER Coaxial "O" Crimp Hand Tool assembly 58433-1, which includes dies 58435-1.

³Order AMP PRO-CRIMPER Coaxial Hex Crimp Hand Tool assembly 58433-2, which includes dies 58436-1.

⁴For use with Belden 9907, Comm/Scope 3104, Belden 8219 only.

⁵For use with Belden 89907, Comm/Scope 2104 only.