

Type C Vertical Receptacle Assemblies with Solder Posts for PC Board Mount
(Continued)

Half Size

Number of Positions	Rows Loaded	Dimensions				Post Length	DIN Level	Part Number
		A	B	C	D			
48	A,B,C	53.34 2.100	49.37 1.944	38.10 1.500	44.35 1.746	2.49 .098	II	535091-5 536397-5 ¹ 1393640-7
						2.90 .114	II	8-1393640-5 8-1393640-2 ¹ 9-1393642-3 ²
						3.30 .130	II	535070-5 535070-4 536484-5 ¹
						4.50 .177	I	2-1393640-1
						4.50 .177	II	2-1393641-5 2-1393641-3 ¹
						4.57 .180	II	535071-5 535071-4 536485-5 ¹
						13.00 .512	II	1393642-9
						2.49 .098	II	650459-5
						2.90 .114	II	8-1393640-6
						4.50 .177	II	2-1393641-6 2-1393641-4 ¹
						4.57 .180	II	650466-4 650466-5

Third Size

Number of Positions	Rows Loaded	Dimensions				Post Length	DIN Level	Part Number
		A	B	C	D			
30	A,B,C	39.76 1.565	34.76 1.368	22.86 .900	29.12 1.146	2.90 .114	II	9-1393642-11, ²
						4.50 .177	II	2-1393641-0 2-1393641-2 ¹
						2.90 .114	II	8-1393640-2 ¹
20	A,C	39.76 1.565	34.76 1.368	22.86 .900	29.12 1.146	4.50 .177	I	2-1393640-0

Expanded Size

Number of Positions	Rows Loaded	Dimensions				Post Length	DIN Level	Part Number
		A	B	C	D			
120	A,B,C	114.30 4.500	110.31 4.343	99.06 3.900	105.31 4.146	2.49 .098	II	535097-5 536489-5 ¹
						3.30 .130	II	535098-5 535098-4 536494-5 ¹
						2.49 .098	II	650404-5
150	A,B,C	139.70 5.500	135.71 5.343	124.46 4.900	130.71 5.146	3.30 .130	II	650405-5
						4.57 .180	II	650406-5

¹ With Boardlocks
² Flux tight

Note: Select load available upon request, contact Product Engineering.

Type C Assemblies