



2041376-2 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

PCB Mounted Jacks - Single Port, Multi-port and Stacked

RJ45 W LED 2X2,30u",DIP,H=25.4mm

2041376-2

TE Internal Number: 2041376-2

Product Highlights [View All](#)

- Connector
- Preloaded
- 2 x 2 Jack Configuration
- Jack Type = RJ45
- PCB Mounting Orientation = Side Entry (Right Angle)

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#)

[Features](#)

[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Jack Type [?]	RJ45
PCB Mounting Orientation [?]	Side Entry (Right Angle)
PCB Mount Style [?]	Through Hole
Performance Category [?]	Cat 3
LED [?]	With
Grounding Options [?]	Panel Ground and PCB Ground
Panel Stops [?]	Without
Keyed [?]	No
Profile [?]	Standard
Color [?]	Black
Mechanical Attachment	
Panel Mount Retention [?]	Without
Termination Features	
Termination Method to PC Board [?]	Solder
Dimensions	
Height (mm [in]) [?]	25.30 [0.996]
PCB Tail Length (mm [in]) [?]	2.54 [0.100]
Body Features	
Inverted Jack Face [?]	No
Shield Plating	Nickel
Contact Features	
Solder Tail Contact Plating [?]	Gold Flash over Nickel
Contact Plating, Mating Area, Material [?]	Gold (30)
Contact Base Material	Phosphor Bronze

Housing Features	
Housing Material	High Temperature Thermoplastic
Configuration Features	
Preloaded	Yes
Jack Configuration [?]	2 x 2
Shielded [?]	Yes
Number of Contacts Loaded	8
Number of PCB Ground Tabs	4
Industry Standards	
RoHS/ELV Compliance [?]	Not reviewed for ELV/RoHS compliance
Lead Free Solder Processes [?]	Not reviewed for lead free solder process
UL Flammability Rating	UL 94V-0
Identification Marking	
LED Position 3 Color [?]	None
LED Color; Top Left [?]	Green
LED Color; Top Right [?]	Yellow
LED Color; Bottom Left [?]	Green
LED Color; Bottom Right [?]	Yellow
Packaging Features	
Packaging Method	Tray/Box
Product Availability	
Region	Asia, EMEA, North America
Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

