

1478763-9 Product Details

[Share](#) | [Print](#) | [Email](#)


Cable Clamps

METAL BACKSHELL 9 WAY 45 DE
1478763-9

TE Internal Number: 1478763-9

Active

[View 3D PDF](#)

Product Highlights [View All](#)

- Backshell/Cable Clamp
- Cable Clamp Type = Two-Piece RFI/EMI Shield
- 45° Cable Exit Angle
- Cable Insulation Diameter = 4.00 - 13.00 mm
- 9 Positions

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	Configuration Features
Product Type ? Backshell/Cable Clamp	Number of Positions 9
Cable Clamp Type ? Two-Piece RFI/EMI Shield	Shielded ? Yes
Shell Size ? 1	Number of Grommets Per Set 4
Screws and Retainer Clips ? With	
Grommets ? With	
Slide Latch ? Without	
Thread Size 4-40	
Product Series ADK	
	Industry Standards
	RoHS/ELV Compliance ? RoHS compliant, ELV compliant
	Lead Free Solder Processes ? Not relevant for lead free process
	RoHS/ELV Compliance History Always was RoHS compliant
	Packaging Features
	Packaging Method ? Loose Piece
	Other
	Brand AMP
	Comment Kit includes backshells, jackscrews and cable grommets.
Dimensions	
Cable Insulation Diameter (mm [in]) ? 4.00 - 13.00 [0.158 - 0.512]	
Body Features	
Cable Exit Angle ? 45°	
Cable Clamp Material Die Cast	
Shield Plating Nickel	

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)