



What can we help you find?

Home > Products > Product Feature Selector > Product Details

1-487769-0 Product Details

Share Print Email



1-487769-0

TE Internal Number: 1-487769-0
 Active

View 3D PDF

Flexible Film Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Socket
- 2.54 mm Centerline

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ View Mating Products (12)
- ▶ View Contacts (17)
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- HOUSING, RECEPTACLE, DETENT, POLARIZED, FFC (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- Connector, Flexible Flat Conductor Cable, .100 Inch ... (PDF, English)

Application Specifications:

- Flexible Flat Cable (FFC) Housings with Contact Cavi... (PDF, English)

Instruction Sheets:

- Extraction Tools (PDF, English)

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version W)
- 3D Model (IGES, Version W)
- 3D Model (STEP, Version W)

Additional Information:

- Product Line Information

Additional Product Images:

- Typical Application

Related Products:

- Tooling
- Mating Products (12)
- Contacts (17)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = Housing
- Type of Connector = Slimline
- Wire/Cable Type = FFC
- Mating Connector Lock = With
- Mating Connector Lock Type = Detent
- Flame Retardant = Yes

Mechanical Attachment:

- Panel Mount Retention = Without
- Mounting Ears = Without

Contact Features:

- Contact Type = Socket

Housing Features:

- Connector Style = Receptacle
- Centerline (mm [in]) = 2.54 [0.100]
- Mating Alignment = Without
- Housing Material = Thermoplastic - GF
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Number of Positions = 12
- Number of Rows = Single

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Cable

Other:

- Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

