



+ CONNECTORS

COMPACTFLASH



✓ Active

TE CONNECTIVITY (TE)

CF HDR,VERT,TYPE 1,SMT,25MM PROFILE,SN10

Compact Flash | SC10

146540-2

TE Internal Number: 146540-2

EU RoHS Compliant

EU ELV Compliant

Number of Positions 50

Centerline (Pitch) 1.27 mm [.05 in]

Number of Rows 2

PCB Mounting Style Surface Mount - Inline leads, Surface Mount

Mounting Angle Vertical

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

PIN HEADER ASSEMBLY, VERTICAL, 50 POSN, SURFACE MOUNT,

PDF

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_146540-2_08092016639_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Profile Low

Shielded No

PCB Offset 0 mm [0 in]

CompactFlash Product Type Header Only

Product Type Removable Memory Products

Format CompactFlash

Configuration Features

Number of Positions 50

Number of Rows 2

Lead Configuration Inline

Body Features

Hold-Downs Without

Color Black

Contact Features

Solder Tail Contact Plating Material Tin

Underplate Material Nickel

Vacuum Tape Without

Contact Base Material Brass

Contact Mating Area Plating Material Gold

Mechanical Attachment

PCB Mounting Style Surface Mount - Inline leads, Surface Mount

Mounting Angle Vertical

Housing Features

Centerline (Pitch) 1.27 mm [.05 in]

Housing Material LCP (Liquid Crystal Polymer)

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Method Box & Tray, Tray

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
