



## ANTENNAS



✓ Active

TE CONNECTIVITY (TE)

# POLYCOM MOLDED STAMPED ANTENNA

Antennas

1513454-1

TE Internal Number: 1513454-1

EU RoHS Compliant with Exemptions

EU ELV Compliant with Exemptions

**Wireless Application** DECT EU

**Mounting Style** Printed Circuit Board

**Connection Type** Surface Mount (SMT)

**Bands** Single Band

**Antenna Style** Embedded

↓ **PRODUCT DRAWING**  
English

↓ **3D PDF**

## DOCUMENTATION

Product Drawings

### DECT EU Antenna

PDF (TIFF AVAILABLE)

English

CAD Files

### 3D PDF

PDF

3D

### Customer View Model

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Connection Type** Surface Mount (SMT)

**Product Type** Antenna

### Configuration Features

**Bands** Single Band

**Antenna Style** Embedded

**Antenna Type** Stamped

### Electrical Characteristics

**Impedance ( $\Omega$ )** 50

**VSWR (Max)** <3:1

### Signal Characteristics

**Gain (Max) (dB)** 2

**Frequency Band (MHz)** 1880 – 1900

### Body Features

**Weight** 1 g [ .035 oz ]

### Mechanical Attachment

**Mounting Style** Printed Circuit Board

**Polarization** Linear

**Region** EU

### Dimensions

**Height** 6.05 mm [ .238 in ]

**Diameter** 16 mm [ .63 in ]

### Operation/Application

**Wireless Standard** DECT EU

### Industry Standards

**Wireless Application** DECT EU

---

Packaging Features

**Packaging Method** Tape & Reel

---

**PRODUCT COMPLIANCE**



Statement of Compliance

**Statement of Compliance**

PDF

---