

## 183073-1 Product Details

[Live Product Chat](#)



### 183073-1

TE Part Number: 183073-1

[Active](#)

[Add to Part List](#)

### CPC Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Connector
- Number of Positions = 24
- Plug
- For Use With Socket Contacts
- Not Preloaded

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

### Documentation & Additional Information

#### Product Drawings:

- [C.P.C. plug ass'y std. sex size 23-24 \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A1)
- [3D Model](#) (IGES, Version A1)
- [3D Model](#) (STEP, Version A1)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Contact Arrangement](#)
- [Keying Options](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- [Number of Positions](#) = 24
- [Gender](#) = Plug
- For Use With = Socket Contacts
- Termination Style = Wire
- [Shell Size](#) = 23
- [Shell Type](#) = All Plastic
- [Product Series](#) = Series 1
- [Thread Size](#) = 1-3/8 - 18 UNEF-2A
- [Sealed](#) = No
- CSA Certified = Yes

#### Mechanical Attachment:

- [Preloaded](#) = No
- [VDE Tested](#) = No
- Keying = A

#### Body Related Features:

- [Mount Style](#) = Free Hanging
- UL Rating = Recognized

#### Contact Related Features:

- [Standard or Reverse Gender](#) = Standard
- Coupling Ring Diameter (mm [in]) = 44.70 [1.760]

#### Housing Related Features:

- Housing Material = Nylon 6/6 GF
- Housing Color = Black
- Housing Flammability Rating = UL 94V-0

#### Configuration Related Features:

- [Reverse Numbering](#) = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = AMP