

1838282 -3 Product Details

[Live Product Chat](#)



1838282 -3

TE Part Number: 1838282 -3

[Active](#)

[Add to Part List](#)

M8/M12 Connector System

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Lead Assembly
- ? Lead Assembly Type = Cable
- ? Wire Size = 0.34 (22 AWG) mm² [AWG]
- ? Number of Positions = 3
- ? Cable Length = 5.00 M

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [M8 STRAIGHT FEMALE CONNECTOR WITH STRAIN RELIEF 3 PO...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Lead Assembly
- ? [Wire Size \(mm² \[AWG\]\)](#) = 0.34 (22 AWG)
- ? [Number of Positions](#) = 3
- ? Insulation Material = PVC
- ? Thread Size = M8
- ? Shielded = No
- ? Gender = Female
- ? Mount Angle = Straight

Mechanical Attachment:

- ? Panel Mount = No

Body Related Features:

- ? [Lead Assembly Type](#) = Cable
- ? [Cable Length \(M \[ft\]\)](#) = 5.00 [16.404]
- ? Cable Color = Black
- ? Connector Color = Black
- ? Wire Color = Brown, Blue, Black
- ? [LED](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Quantity = 20

Other:

- ? Brand = Tyco Electronics