



CONNECTORS

D-SUB BACKSHELLS & CLAMPS



✓ Active

TE CONNECTIVITY (TE)

METAL BACKSHELL 25 WAY 45 DE

AMPLIMITE | Solder Cup Connectors

2-1478763-5

TE Internal Number: 2-1478763-5

EU RoHS Compliant

EU ELV Compliant

Cable Insulation Diameter 4 – 13 mm [.197 – .355 in]

Accessory Type Backshell

Cable Clamp Type Two-Piece RFI/EMI Shield

Number of Positions 25

Shell Size 3

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

ADK SERIES DIE-CAST BACKSHELL 45 DEGREE ENTRY

PDF

English

LEAFLET ASSEMBLY INSTRUCTIONS ADK BACKSHELL

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_2-1478763-5_08122016647_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type Backshell

Shell Size 3

Shielded Yes

Slide Latch Without

Grommets With

Thread Size 4-40

Configuration Features

Number of Positions 25

Body Features

Cable Clamp Type Two-Piece RFI/EMI Shield

Cable Exit Angle 45

Grommets per Set 4

Cable Clamp Material Die Cast

Shield Plating Material Nickel

Backshell Material Zinc

Mechanical Attachment

Screws and Retainer Clips With

Dimensions

Cable Insulation Diameter 4 – 13 mm [.197 – .355 in]

Industry Standards

Cover Flammability Rating UL 94V-2

Packaging Features

Packaging Method Bag

Packaging Quantity 100

Other

Comment Kit includes backshells, jackscrews and cable grommets.

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
