

3-1393816-4 Product Details



3-1393816-4

TE Part Number: 3-1393816-4

✓ Active

➤ [Add to Part List](#)

Communications/Signal PC Board Relays

✓ [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- V23005/Cradle Relay W Series
- AC Actuating System
- Input Voltage = 110 VAC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 5 Amps.

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Cradle W Relay Datasheet](#) (PDF, English)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Termination Type = Solder/Plug-In Terminals

Electrical Characteristics:

- Actuating System = AC
- Input Voltage (VAC) = 110
- Contact Current Rating (Amps.) = 5
- [Coil Resistance \(Ω\)](#) = 3200
- Coil Power, Nominal (VA) = 0.70 - 1.15
- Dielectric Between Coil and Contacts (V rms) = 2000

Body Related Features:

- [Series](#) = V23005/Cradle Relay W
- Polarized = No

Contact Related Features:

- Mounting Options = Socket
- Enclosure = Dust Protected
- [FCC Part 68 Isolation](#) = No
- Approved Standards = None
- Contact Material = Silver, Gold Overlay
- Approx. Dimensions (L x W x H) (mm [in]) = 30.00 x 19.00 x 40.00 [1.181 x .748 x 1.575]
- Compatible Socket = With
- Contact Type = Single
- Pin Configuration = Industry Standard

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- [Coil Magnetic System](#) = Non Polarized, Monostable
- Coil Suppression Diode = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Other:

- Brand = Axicom