


## 324369 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**324369**

[Active](#)

### Splices - Closed Barrel

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Splice
- ? Not Sealed
- ? Splice Type = Butt
- ? Butt Splice Type = Strap
- ? Body Style = SOLISTRAND

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [SPLICE, BUTT, STRAP, SOLISTRAND](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? [Product Type](#) = Splice
- ? [Sealed](#) = No
- ? [Splice Type](#) = Butt
- ? [Body Style](#) = SOLISTRAND
- ? [Insulation](#) = No
- ? [Insulation Support](#) = Non -Insulation Support
- ? [Material](#) = Copper
- ? Finish = Gold (50)
- ? Color = None

#### Mechanical Attachment:

- ? Inside Diameter (mm [in]) = 0.79 [0.031]

#### Body Related Features:

- ? [Butt Splice Type](#) = Strap
- ? [Wire Range \(mm \[AWG\]\)](#) = 0.12 -0.40 <sup>2</sup> [26-22]
- ? [Wire Range \(CMA\)](#) = 202 - 810
- ? Stock Thickness (mm [in]) = 0.51 [0.020]
- ? Outside Diameter (mm [in]) = 2.08 [0.082]

#### Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

#### Other:

- ? Brand = AMP