

# 41969-2 Product Details

[Share](#) | [Print](#) | [Email](#)


## FASTON Uninsulated Receptacles & Housings

FASTON PREM. REC LP  
41969-2   
TE Internal Number: 41969-2

Active

[View 3D PDF](#)

**Product Highlights** [View All](#)

- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.81 mm
- Board Mount = No
- Receptacle Style = Straight

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**  
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Terminal
Receptacle Style	Straight
Insulation Support	Insulation Support
Wire/Cable Type	Stranded
Insertion Force	Normal
Finish	Tin
Mechanical Attachment	
Board Mount	No
Termination Features	
Crimp Type	F-Crimp
Dimensions	
Mating Area Interface Dimensions (mm [in])	6.35 x 0.81 [.250 x .032]
Insulation Diameter (mm [in])	2.29-3.30 [.090-.130]
Body Features	
Weld Tab	Without
Wire Range (mm [AWG])	0.30-0.90 <sup>2</sup> [22-18]
Material	Brass
Stock Thickness (mm [in])	0.46 [0.018]

Contact Features	
Terminal Type	Receptacle
Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Listed
CSA Certified	Yes
Conditions for Usage	
For Hermetic Header Tab	No
Packaging Features	
Packaging Method	Loose Piece
Other	
Line	Premier
Brand	AMP
Comment	Wire barrel pre-crimped.

**Related Products**

Not quite the product you're looking for?  
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)