

5205738 -7 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



5205738 -7

Active

Standard Board Mount Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Number of Positions = 25
- ? Receptacle
- ? PCB Mount Angle = Vertical
- ? Product Series = HDP -20
- ? Without Mating Connector Lock

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Mating Products \(9\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE ASSEMBLY, SIZE 3, 25 POSN, VERTICAL, AMPL...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [AMPLIMITE HD -20 PCB Mounted Connector](#) (PDF, English)

Application Specifications:

- ? [AMPLIMITE HD -20 Straight Solder Contact Tine, Front ...](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version B)
- ? [3D Model](#) (IGES, Version B)
- ? [3D Model](#) (STEP, Version B)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Mating Products \(9\)](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Number of Positions](#) = 25
- ? [Gender](#) = Receptacle
- ? [PCB Mount Angle](#) = Vertical
- ? [Product Series](#) = HDP -20
- ? [Mating Connector Lock](#) = Without
- ? [PCB Retention Feature](#) = No
- ? [Shell Type](#) = Full Metal
- ? [Shell Size](#) = 3
- ? [PCB Thickness \(in \[mm\]\)](#) = 0.062 [1.57], 0.093 [2.36]
- ? [Grounding Indents](#) = Without
- ? [Grounding Straps](#) = Without
- ? [PCB Mount Style](#) = Thru Hole
- ? [Color Code](#) = None
- ? Sealed = No
- ? Profile = Standard
- ? Post Size (mm [in]) = 0.64 [.025]
- ? Shell Material = Steel

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Termination Related Features:

- ? [Grounding Clips](#) = Without
- ? [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 4.78 [0.188]
- ? [Solder Tail Contact Plating](#) = Tin

Body Related Features:

- ? Insert Flammability Rating = UL 94V -0
- ? Insert Material = Polyamide, GV
- ? Shell Plating = Zinc

Contact Related Features:

- ? [Contact Mating Area Plating Material](#) = Gold (30), Gold Flash over Palladium Nickel
- ? Contact Shape = Square
- ? Contact Material = Phosphor Bronze

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? Application = Standard

Other:

- ? Brand = AMP