


5788796-3 Product Details

[Live Product Chat](#)



5788796-3

TE Part Number: 5788796-3

Active

[Add to Part List](#)

Standard Board Mount Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Number of Positions = 9
- Receptacle
- PCB Mount Angle = Right Angle
- Product Series = HD 20
- With Mating Connector Lock

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(8\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [RCPT ASSEMBLY, SIZE 1, .318 SERIES, WITH FRONT METAL...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 0)
- [3D Model](#) (IGES, Version 0)
- [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)
- [Mating Products \(8\)](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Number of Positions](#) = 9
- [Gender](#) = Receptacle
- [PCB Mount Angle](#) = Right Angle
- [Product Series](#) = HD 20
- [Mating Connector Lock](#) = With
- [Mating Connector Lock Type](#) = Threaded Inserts
- [PCB Retention Feature](#) = Yes
- [Shell Type](#) = Front Metal Shell
- [Shell Size](#) = 1
- [Footprint \(mm \[in\]\)](#) = 8.08 [.318]
- [PCB Thickness \(in \[mm\]\)](#) = 0.062 [1.57]
- [Grounding Indents](#) = Without
- [Grounding Straps](#) = Without
- [PCB Mount Style](#) = Thru Hole
- [Color Code](#) = None
- Sealed = No
- Profile = Standard
- SMT Compatible = Yes
- Shell Material = Steel
- Threaded Insert Material = Zinc
- Eyelet Material = Brass

Mechanical Attachment:

- [Panel Attachment](#) = Without
- Boardlock Material = Copper Alloy
- Boardlock Plating = Tin

Termination Related Features:

- [Grounding Clips](#) = Without
- [Termination \(Solder\) Post Length \(mm \[in\]\)](#) = 3.18 [0.125]
- [Solder Tail Contact Plating](#) = Tin over Nickel

Body Related Features:

- [PCB Retention Method](#) = Boardlock(s)
- Shell Plating = Tin
- Threaded Insert Plating = Clear Chromate
- Eyelet Plating = Tin

Contact Related Features:

- [Contact Mating Area Plating Material](#) = Gold (30)
- Contact Material = Copper Alloy

Housing Related Features:

- Housing Flammability Rating = UL 94V-0
- Housing Material = Thermoplastic

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- High Temperature Housing = Yes

Packaging Related Features:

- Packaging Method = Tube

Other:

- Brand = AMP