

## 606298 -2 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**606298 -2**

✓ [Active](#)

### Heavy Duty Drawn Electrical Lugs

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Ring
- ? Wire Barrel Style = Chamfered
- ? Terminal Shape = Tubular Ring
- ? Wire Size (AWG/CM) = 4/0 AWG
- ? Stud Size = 1/2

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [AMP TUBULAR TERMINAL 4/0 \(ROUND TONGUE\)](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features

(Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Product Type = Ring
- ? Terminal Shape = Tubular Ring
- ? Stud Size = 1/2
- ? Body Style = Straight
- ? Color Code = No
- ? UL Recognized = Yes
- ? Comment = Starter End

#### Electrical Characteristics:

- ? Wire Barrel Style = Chamfered
- ? Sight Hole = Without

#### Body Related Features:

- ? Wire Size (AWG/CM) = 4/0 AWG
- ? Plating = Tin
- ? Wire Barrel I.D. (mm [in]) = 16.76 [0.660]

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- ? Brand = AMP