



CALIBRATION LABELS



✓ Active

TE CONNECTIVITY (TE)

QC143

QC143

TE Internal Number: 1878655-1

Always EU RoHS/ELV Compliant

Label Height **12.7 mm [.5 in]**

Label Width **50.8 mm [2 in]**

Label Style **Calibration**

Label Color **Green**

Label Finish **Matte**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Self-Laminating	No
	Tamper Evident	No
	Product Type	Q-CEE Label

Body Features	Material	Vinyl
---------------	----------	--------------

Usage Conditions	Operating Temperature Range	-40 – 80 °C [-40 – 176 °F]
------------------	-----------------------------	-------------------------------------

Operation/Application	Energy Product	No
-----------------------	----------------	-----------

Printer/Label Features	Label Height	12.7 mm [.5 in]
	Label Width	50.8 mm [2 in]
	Label Style	Calibration
	Label Color	Green
	Label Finish	Matte
	Adhesive Type	Removable
	Label Type	Die-Cut (on Sheets)
	Printer Type	Hand writable



Product Availability

Region

Americas

Packaging Features

Packaging Quantity

160

Other

Configurator Part

No


Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

Customers Also Bought

WIRE-TO-BOARD HEADERS & RECEPTACLES	SIGNAL RELAYS	SPLICES	PCB TERMINALS
 <p>14P MTA100 HDR ASSY (NARROW) 4-644456-4</p>	 <p>V23079G2001B301 V23079G2001B301</p>	 <p>PG BUTT SPLC 22-16COMM22-18MIL 34203</p>	 <p>.058 DIA PIN PC PTPPHBZ 60802-2</p>