



PLUGGABLE I/O CABLE ASSEMBLIES



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE) CA 75MM 12 POS. MOW-PB M-M VALUE LINE

2205116-1
TE Internal Number: 2205116-1

Always EU RoHS/ELV Compliant


Cable Assembly Type **MOW to PB**

Equalized **No**

Wire Size (AWG) **28**

Cable Assembly Length **.075 m [.246 ft]**

Color **Gray**



Product Drawings

CABLE ASSY MICRO-MATCH MOW-PB VALUE-LINE

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Assembly Type	MOW to PB
Product Type	Cable Assembly
Cable Assembly Category	Industry Standard
Product Designation	Patch Cord

Configuration Features

Number of Power Positions **12**

Keyed	No
Configuration	Double-Ended

Body Features	Equalized	No
	Color	Gray

Dimensions	Wire Size (AWG)	28
	Cable Assembly Length	.075 m [.246 ft]

Industry Standards	Flammability Rating	UL 2651
	IEEE 1394	No

Other	CLOUDSPLITTER	No
-------	---------------	-----------

Product Compliance	Statement of Compliance
	PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

