


[My Cart](#)

[My Part Lists](#)
[Sign In/Register](#)

[English \(Change\)](#)
Have a Question?

Chat with a Product Information Specialist


[Products](#)
[Industries](#)
[Resources](#)
[About TE](#)
[Support Center](#)
[My Account](#)
[Home](#) > [Products](#) > [Switches & Knobs](#) > [Product Feature Selector](#) > Product Details

[Share](#)

[Print](#)

[Email](#)

4-1825139-5 Product Details


4-1825139-5

TE Internal Number: 4-1825139-5

Active

Toggle Switches


[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- A Series
- Double Pole - Three Throw Configuration (Pole-Throw)
- Current Rating = 5 A
- Mount Style = Panel
- Termination Type = Vertical, Wire Lugs

[View all Features](#)
[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [GEMINI A SERIES TOGGLE SWITCH, DOUBLE POLE, 3 POSITI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES_CORE_PROGRAM_CATALOG](#) (PDF, English)
- [GEMINI SERIES SWITCHES QUICK REF GUIDE 2-1773458-5](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Series = A
- Configuration (Pole-Throw) = Double Pole - Three Throw
- Termination Type = Vertical, Wire Lugs

Electrical Characteristics:

- Current Rating (A) = 5

Termination Features:

- Seal Type = Terminal Seal (Insert Molded)

Body Features:

- Mount Style = Panel

Contact Features:

- Contact Plating = Silver

Housing Features:

- Toggle Style = Baton Standard
- Toggle Length (mm [in]) = 10.40 [0.410]
- Process Sealed = No
- Bushing Style = Threaded
- Bushing Type = 1/4-40
- UL Flammability Rating = UL 94V-0

Configuration Features:

- [Operating Function](#) = (On) On (On)

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch

- Comment = UL available when ordering - consult factory.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

