



1825096-7 Product Details

[Share](#) | [Print](#) | [Email](#)


1825096-7

TE Internal Number: 1825096-7
✔ Active

Pushbutton Switches

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Switch
- Not Tactile
- Single Pole - Double Throw Configuration (Pole-Throw)
- Contact Rating = 0.4VA
- Operating Function = Momentary

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[View 3D PDF](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [PUSHBUTTON SWITCH, TPA SERIES \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- [SWITCHES_CORE_PROGRAM_CATALOG \(PDF, English\)](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version A\)](#)
- [3D Model \(IGES, Version A\)](#)
- [3D Model \(STEP, Version A\)](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Switch
- Tactile = No
- Series = TPA
- Mount Angle = Vertical
- Termination Type = Printed Circuit
- Actuator Style = Round

Electrical Characteristics:

- Contact Rating = 0.4VA

Dimensions:

- Actuator Length (mm [in]) = 3.85 [0.152]

Body Features:

- Mount Style = Through-Hole
- Actuator Profile = Extended
- Actuator Color = Black
- Case Material = Polyester
- Actuator Material = Polyamide

Contact Features:

- Contact Plating = Gold over Nickel

Housing Features:

- Process Sealed = No
- Low Profile = No

Configuration Features:

- Configuration (Pole-Throw) = Single Pole - Double Throw
- Operating Function = Momentary
- Ganged = No
- ESD Grounding Terminal = Without
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- Temperature Rating = High

Operation/Application:

- Actuator Force (g [oz]) = 50.00 - 400.00 [1.770 - 14.120]

Packaging Features:

- Packaging Method = Loose Piece

Other:

- Brand = Alcoswitch