

## 1571984-1 Product Details

### Have a Question?

Chat with a Product Information Specialist



**1571984-1**

TE Internal Number: 1571984-1

Active

[View 3D PDF](#)

### Slide Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- 2 Positions
- Single Pole - Double Throw Configuration (Pole-Throw)
- Actuator Style = Extended, Side
- Actuator Color = Black
- TSS Series

[View all Features](#)

**onlinecomponents.com**  
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [SLIDE SWITCH RA](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A1)
- [3D Model](#) (IGES, Version A1)
- [3D Model](#) (STEP, Version A1)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Configuration (Pole-Throw) = Single Pole - Double Throw
- Actuator Style = Extended, Side
- Mount Angle = Right Angle
- Terminal Configuration = Standard
- Termination Type = PC

#### Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

#### Body Related Features:

- [Number of Positions](#) = 2
- Actuator Color = Black
- Series = TSS
- Mount Style = Through-Hole
- PCB Tail Length (mm [in]) = 3.30 [0.130]
- Actuator Material = Polyester

#### Contact Related Features:

- Contact Plating = Gold
- Contact Base Material = Copper

#### Housing Related Features:

- UL Flammability Rating = UL 94V-0

#### Configuration Related Features:

- Operating Function = On None On
- Number of Actuators = Single

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Identification Marking:

- Stamped Marking = With

#### Other:

- Brand = Tyco Electronics

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

Follow us on: