


4-1825059-1 Product Details

Have a Question?

Chat with a Product Information Specialist



4-1825059-1
(ADF0BST04)

TE Internal Number: 4-1825059-1

Active

[View 3D PDF](#)

DIP, Rotary DIP, SIP Switches and DIP Shunts - Standard

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- Switch - Mechanical
- Switch Type = DIP
- PCB Mount Style = Surface Mount
- Single Pole - Single Throw Configuration (Pole-Throw)
- Actuator Style = Flush, Slide

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [DIP SWITCH, ADF-SMT SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Switch - Mechanical
- [PCB Mount Style](#) = Surface Mount
- [Configuration \(Pole-Throw\)](#) = Single Pole - Single Throw
- [Actuator Style](#) = Flush, Slide
- Sealed = Yes
- [Number of Switches](#) = 8
- Termination Style = Outside "L"

Termination Related Features:

- Seal Type = Tape

Body Related Features:

- Switch Type = DIP
- Series = AD
- Centerline (mm [in]) = 2.54 [0.100]

Contact Related Features:

- Auto-Insertable = Yes
- Contact Base Material = Copper Alloy
- Contact Plating, Mating Area, Material = Gold Flash

Housing Related Features:

- Housing Color = Black
- Housing Material = PPS
- UL Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Package
- Packaging Quantity = 20

Other:

- Brand = Tyco Electronics

BOOKMARK

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

