

MRJE3404 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Rotary Switches

MRJE3404

MRJE3404

TE Internal Number: 1825537-3

Product Highlights [View All](#)

- 4 Positions
- Angle of Throw = 15.00 °
- Actuator Style = Long Thin Knob
- Code Type = 3 Poles
- Straight Mount Angle

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Angle of Throw (°) ?	15.00
Actuator Style ?	Long Thin Knob
Code Type ?	3 Poles
Mount Angle ?	Straight
Product Series	MRJE

Electrical Characteristics	
Contact Rating	0.4VA

Contact Features	
Solder Tail Contact Plating	Gold over Nickel
Contact Base Material	Brass

Housing Features	
Housing Material	Epoxy

Configuration Features	
Number of Positions ?	4

Industry Standards	
RoHS/ELV Compliance ?	RoHS compliant, ELV compliant
Lead Free Solder Processes ?	Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
RoHS/ELV Compliance History	Always was RoHS compliant

Other	
Brand	Alcoswitch
Comment	Fixed

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)