

TOGGLE SWITCHES



✓ Active

TE CONNECTIVITY (TE) A208P3ZQ04

Alcoswitch | A

3-1825138-3

TE Internal Number: 3-1825138-3

Alias ID: A208P3ZQ04

EU RoHS Compliant with Exemptions EU ELV Compliant with Exemptions

Configuration (Pole-Throw) Double Pole - Double Throw

Bushing Thread Size 1/4-40 UNS-2A

Sealed Yes

Contact Base Material Copper

Contact Plating Silver



PRODUCT DRAWING

DOCUMENTATION

Product Drawings

GEMINI A SERIES TOGGLE SWITCH, DOUBLE POLE, 2 POSITION FUNCTIONS (01 & 08)

PDF

English

Catalog Pages/Data Sheets

SWITCHES_CORE_PROGRAM_CATALOG

PDF

English

GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5

PDF

English

+

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealed Yes

Toggle Style Large Flat with Bushing

Switch Type Toggle

Toggle Actuation Vertical

Product Type Switch

Configuration Features

Configuration (Pole-Throw) Double Pole - Double Throw

Operating Function On (On)

Electrical Characteristics

Contact Resistance ($m\Omega$) 10

Voltage Rating 125 VAC, 28 VDC

Insulation Resistance (M Ω) 1000

Dielectric Strength (VAC) 1000

Body Features

Bushing Thread Size 1/4-40 UNS-2A

Seal Type Terminal Seal (Epoxy)

Bushing Style Threaded

Actuator Finish Nickel

Contact Features

Contact Base Material Copper

Contact Plating Silver

Contact Current Rating (A) 5

Termination Features

Termination Type Wire Lugs

Mechanical Attachment

Mounting Type Solder

Housing Features

Process Sealed No

Dimensions

Bushing Length (in) .28

Toggle Length 12.32 mm [.485 in]

Statement of Compliance

Statement of Compliance

PDF