

## 1571100-2 Product Details

**Have a Question?**

[Chat with a Product Information Specialist](#)

[Chat with a Product Information Specialist](#)



**1571100-2**

TE Internal Number: 1571100-2

**Active**

### Rocker/Paddle Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Contact Rating = 10A @ 277 VAC 3/4 hp, 10A @ 250 VAC, 12A @ 125 VAC 3/4 hp, 20A @ 125 VAC
- Single Pole - Double Throw Configuration (Pole-Throw)
- Silver Tin Oxide Contact Plating
- PRC Series
- Operating Function = On On

[View all Features](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN PANEL CUT-...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Configuration (Pole-Throw) = Single Pole - Double Throw
- Actuator Style = Rocker
- Actuator Type = Top
- Termination Type = Quick Connect
- Mount = Panel
- UL Listed = File No. E46765

#### Electrical Characteristics:

- Contact Rating = 10A @ 277 VAC 3/4 hp, 10A @ 250 VAC, 12A @ 125 VAC 3/4 hp, 20A @ 125 VAC

#### Body Related Features:

- Series = PRC
- Actuator Color = Black
- Mount Style = 21.20mm x 36.60mm [.835 in. x 1.441 in.] Panel Cutout, 21.20mm x 36.80mm [.835 in. x 1.448 in.] Panel Cutout, 21.20mm x 37.00mm [.835 in. x 1.456] Panel Cutout
- LED = Without
- Terminal Tab Width (mm [in]) = 6.35 [0.250]

#### Contact Related Features:

- Contact Plating = Silver Tin Oxide

#### Housing Related Features:

- Process Sealed = Yes

#### Configuration Related Features:

- Operating Function = On On
- Indicator/Imprint Color = White
- Indicator/Imprint Legend = - -
- Beveled Frame Color = Black

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = UL, UL Recognized for Canada and US

#### Purchasing Information:

- Lamp = Without

#### Other:

- Brand = Tyco Electronics
- Comment = Non-Illuminated.; IP66

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

