

1571102-2 Product Details

Have a Question?

[Chat with a Product Information Specialist](#)



[Chat with a Product Information Specialist](#)



1571102-2

TE Internal Number: 1571102-2

[Active](#)

Rocker/Paddle Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Contact Rating = 10A @ 277 VAC 3/4 hp, 10A @ 250 VAC, 12A @ 125 VAC 3/4 hp, 20A @ 125 VAC
- Double Pole - Single Throw Configuration (Pole-Throw)
- Silver Tin Oxide Contact Plating
- PRC Series
- Operating Function = On Off

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN PANEL CUT-...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw
- Actuator Style = Rocker
- Actuator Type = Top
- Termination Type = Quick Connect
- Mount = Panel
- UL Listed = File No. E46765

Electrical Characteristics:

- Contact Rating = 10A @ 277 VAC 3/4 hp, 10A @ 250 VAC, 12A @ 125 VAC 3/4 hp, 20A @ 125 VAC

Body Related Features:

- Series = PRC
- Actuator Color = Black
- Mount Style = 21.20mm x 36.60mm [.835 in. x 1.441 in.] Panel Cutout, 21.20mm x 36.80mm [.835 in. x 1.448 in.] Panel Cutout, 21.20mm x 37.00mm [.835 in. x 1.456] Panel Cutout
- LED = Without
- Terminal Tab Width (mm [in]) = 6.35 [0.250]

Contact Related Features:

- Contact Plating = Silver Tin Oxide

Housing Related Features:

- Process Sealed = Yes

Configuration Related Features:

- Operating Function = On Off
- Indicator/Imprint Color = White
- Indicator/Imprint Legend = O -
- Beveled Frame Color = Black

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Approved Standards = UL, UL Recognized for Canada and US

Purchasing Information:

- Lamp = Without

Other:

- Brand = Tyco Electronics
- Comment = Non-Illuminated.; IP66

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Follow Us On:



Visit Us On:

