






TERM	TYPE	PANEL & °C
L K 2.8 H 4.8 C 6.3	(C) 0177 00 Chrome bezel  KEMA KEUR RU	Ø 12.7 12.0max page 66
L K 2.8 H 4.8 C 6.3	(C) 0067 00 Chrome bezel  RU	Ø 12.7 1.14max page 66
L K 2.8 H 4.8 C 6.3	(C) 0180AA  SE	Ø 12.7 19.0max page 66
L K 2.8 H 4.8 C 6.3	(C) 0180BB Chrome bezel  SE	Ø 13.5 0.9-1.14 page 66
L K 2.8 H 4.8 C 6.3	(C) 0579 00  KEMA KEUR RU	Ø 14.0 2.5max page 66

DIMENSIONS (mm)

