



Note for plug:

- Material: Housing-polycarbonate, clear.
- Terminal-0.36[.014] thick phosphor bronze. Thick gold in localized gold plate.
- Area, Gold Flash over the remainder.
- Over 2.54mm[.000100] thick nickel underplate.

Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length
AT-S-26-6/4/B-5/R	A	1,525±20(5ft)	Black	1,525-1,535mm
AT-S-26-6/4/B-7/R	B	2,135±30(7ft)	Black	2,135-2,145mm
AT-S-26-6/4/B-10/R	C	3,050±60(10ft)	Black	3,050-3,060mm
AT-S-26-6/4/B-12/R	D	3,660±60(12ft)	Black	3,660-3,670mm
AT-S-26-6/4/B-14/R	E	4,270±60(14ft)	Black	4,270-4,280mm
AT-S-26-6/4/B-25/R	F	7,625±100(25ft)	Black	7,625-7,635mm
AT-S-26-6/4/B-50/R	G	15,250±150(50ft)	Black	15,250-15,260mm

P1	P2
1 — BLACK	1
2 — RED	2
3 — GREEN	3
4 — YELLOW	4

SEC: A-A

Unit: mm



Scale	Free																		
TOLERANCE																			
X.	±X																		
X.X	±X																		
X.XX	±X																		
DIM	TOL																		
X.°	±X°																		
X.X°	±X°																		
Angle	TOL	Id.	Modification	Date	Name														



Date	Name	Title
28.06.13	Wilson	Modular cable - Straight/Reversed 6P4C 50µ", 26AWG, Black, 5-50 feet
28.06.13	Groll	ASSMANN WSW-No.
		AT-S-26-6/4/B-xx/R
		Drawing-No.
		rev00
		Sheet
		1/1