

**P1**




Conductor: [26AWG(0.16/7)Bare Copper]x8C

Insulation: [PP6331 ID:0.95±0.03]x8C

Jacket: PVC NOUL 65P

White  
Orange  
Black  
Red  
Green  
Yellow  
Blue  
Brown

P1	COLOR
1	WHITE
2	ORANGE
3	BLACK
4	RED
5	GREEN
6	YELLOW
7	BLUE
8	BROWN



**Note:**

- Material: Housing-polycarbonate, clear
- Terminal-0.36[.014] thick phosphor bronze. Thick gold in localized gold plate. Area, Gold Flash over the remainder.
- Over 2.54mm[.000100] thick nickel underplate.

Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length
AT-S-26-8/8/B-5-OE	A	1,525±20(5ft)	Black	1,525-1,535mm
AT-S-26-8/8/B-7-OE	B	2,135±30(7ft)	Black	2,135-2,145mm
AT-S-26-8/8/B-10-OE	C	3,050±60(10ft)	Black	3,050-3,060mm
AT-S-26-8/8/B-12-OE	D	3,660±60(12ft)	Black	3,660-3,670mm
AT-S-26-8/8/B-14-OE	E	4,270±60(14ft)	Black	4,270-4,280mm
AT-S-26-8/8/B-25-OE	F	7,625±100(25ft)	Black	7,625-7,635mm
AT-S-26-8/8/B-50-OE	G	15,250±150(50ft)	Black	15,250-15,260mm

Scale	Free	Date	Name
TOLERANCE		Drawn	01.07.13 Wilson
X.	±X	Approved	01.07.13 Groll
X.X	±X		
X.XX	±X		
DIM	TOL		
X.°	±X°		
X.X°	±X°		
Angle	TOL		

Title	
Modular cable - Straight/Open	
8P8C 50µ", 26AWG, Black, 5-50 feet	
ASSMANN WSW-No.	
AT-S-26-8/8/B-xx-OE	
Drawing-No.	
rev00	
Replace	Sheet
	1/1



Unit: mm



Id.	Modification	Date	Name