





1 2 3 4 5 6 7



PIN OUT



- Material**
- Cable: SFTP [26AWG(Bare copper)*1PR]*4+Al-foil+braid, PVC
 - OD:5.3±0.3mm
 - RJ45 Connector: 8P8C, Two Fork 3µ" Gold plated contacts, metal housing
 - Molding PVC: 50P
 - Cable/Molding color: Grey
- Electrical**
- Open/short/intermittence: 100%

Order Code: A-MCSSP-80xxx-R
 Order lengths in meter: 0.5,1,2,3,5,7,10,15,20,30

G	Scale					Date	Name	Title Cat5e SFTP Patch cable 26AWG, Grey
	TOLERANCE					Drawn	Wilson	
H	Unit: mm	X. ±X				Approved	Groll	A-MCSSP-80xxx-R
		X.X ±X						Drawing-No.
		X.XX ±X						rev01
		DIM TOL						Sheet
		X.° ±X°	①	Update	19.02.13	Wilson		1/1
		X.X° ±X°		Modification	Date	Name		
		Angle TOL	Id.					



1 2 3 4 5 6 7