



PIN ASSIGNMENT



**Material:**

- Cable: UL2919 28AWG 25P+ADB BE02  
- OD: 9.0
- P1 & P2 Connectors: HPDB-50 Pin(BK)  
- ID:0.62MM  
- IDC Type Molding  
- Hi TEAMP Tape W:20MM
- Inner Molding: PE-5321
- Foil: FOIL-CU-32MM
- Latches/BE02 (Flag Hooks)

Unit: MM



ITEM NO.	<b>AK579/F-1</b>
TITLE	SCSI Cable 2 - 1 Meter, D-Sub 50HP Male <=> D-Sub 50HP Male

**ASSMANN**  
Electronics, Inc.

1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283  
Toll Free: 1-877-277-6266 • Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED  
©Copyright 2010 by Assmann Electronic Components  
All International Rights Reserved