



1 2 3 4 5 6 7



D PIN OUT



- Material**
- Cable: UTP (26AWG*1PR)*4+PVC
- OD:4.9±0.2mm
 - RJ45 Connector: 8P8C, Two Fork 3μ" Gold plated contacts short type two parting
 - Molding PVC: 45P
 - Cable/Molding color: Red, Yellow, Green or Blue
- Electrical**
- Open/short/intermittence: 100%

Order Code: A-MCUP-80xxx/x-R

Order lengths in meter: 0.5, 1, 2, 3, 5, 7, 10, 15, 20, 30

Order color: Red, Yellow, Green, Blue

G	Scale					Date	Name	Title Cat5e UTP Patch cable 26AWG, colored
	TOLERANCE					Drawn	Wilson	
H	Unit: mm					Approved	Groll	ASSMANN WSW-No. A-MCUP-80xxx/x-R
	RoHS Compliant							Drawing-No. rev01
								Replace Sheet 1/1



1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283
Toll Free: 1-877-277-6266 • Email: info@assmann.us

1 2 3 4 5 6 7