



Materials:

- Insulator: P.B.T. Glass Filled, UL94V-0
- Soldering Temperature: 235°C
- Spring Wire: 0.45MM Dia. Phosphor Bronze Gold Plating over Nickel
- Color: Black

Electrical:

- Insulation Resistance: 500MΩ Min.
- Contact Resistance: 20MΩ Max.
- Rating Current: 1.5A Max.
- Rating Voltage: 120V AC
- Dielectric Withstanding: 1,000V AC at 1 Minute
- Operating Temperature: -40°C ~ +85°C
- Durability: 500 Mating cycles Min.

⊗ = Assmann Logo



ITEM NO

A-2014-1-4-R

TITLE

PCB Jack, 6P6C, 180°, Top Entry, 6μ",
with Flange, Black

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED

© Copyright 2009 by Assmann Electronic Components
All International Rights Reserved