


NOTE:

1. CABLE:
 UL2725 80°C 30V [26AWG(1/0.404)*2F
 +AL/MY+DRAIN WIRE(1/0.32)*2]TIN
 INS:FOAM-PE OD:φ1.1±0.05mm
 PVC JACKET OD:φ(2.2±0.1)*(7.8±0.2)mm COLOR:RED (PANTONE 200C)
 PRINT: 2725 E209329 R AWM 80°C 30V VW-1 Serial ATA 26AWG LIAN FENG (BLACK WORD)
 IMPEDANCE: 100±5 OHM (SUPPLIER: LIAN FENG)
2. CONNECTOR:
 2-1 MATERIAL:
 HOUSING: HIGH TEMPERATURE POLYESTER & GLASS FIBER UL 94V-0
 TERMINAL: COPPER ALLOY
 2-1 PLATING:
 CONTACT AREA: 15u" GOLD PLATED
3. HOOD: MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
4. CABLE ASS'Y ELECTRICAL TEST:
 4-1 100% OPEN SHORT & MIS WIRE TEST
 4-2 CONTACT RESISTANCE 2 OHM MAX
 4-3 INSULATION RESISTANCE 20M OHM MIN
5. PACKING: SEE P-0039 REV.C PACKING DRAWING
 (BINDING SIZE MUST BE SMALLER THAN BLISTER)



ITEM NO	AK-SATA-XXXDL-R
TITLE	Serial ATA, 2X Signal, Receptacle, LE, 1 Straight, 1 Down, Left Angle

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283
Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED
© Copyright 2008 by Assmann Electronic Components
All International Rights Reserved