



A
B
C
D
E
F
G
H

A
B
C
D
E
F
G
H



Material:
 • Cable: UL2725, #28X1P+#24Xac+65%Braid, O.D:5.0
 • Connector: USB A Plug

Note:
 1. Total Length: 2000±50mm
 2. Color: Beige
 3. Molded Type



Scale	1:1						Name	Item No. AK670-OE-R (Version 1.1)
TOLERANCE					Drawn	08.29.11	Chappell	
X.X	±0.40				Approved			Title USB Cable A-Male to Open End, 2M
X.XX	±0.25							
X.XXX	±0.15							Drawing No.
Angle	±3°							rev00
								Replace
								Sheet

