


Material:

- Cable: UL2725, T.C #28(7/0.127)x1Pair(Green, White)+ T.C #24(7/0.2)x2C(Red, Black)+AL/MY+Drain+ 65% Braid, Beige PVC O.D:4.7mm
- Connector: USB A Plug

Note:

1. Total Length:0000±50MM
2. Color: Beige
3. Molded Type

Scale	1:1								Name
TOLERANCE									
X.X	±0.40						Drawn	08.29.11	Chappell
X.XX	±0.25						Approved		
X.XXX	±0.15								
Angle	±3°								
									
				Modification	Date	Name			



Item No.
AK670-X-R (Version 1.1)
AK670/2-X-R (Version 2.0)

Title USB Cable A to A, Version 1.1 & 2.0 USB A Male to A Male

Drawing No.	rev00
Replace	
Sheet	