


CABLE BLACK PRINT
 HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
 E189529 ANW STYLE 2725 80° C 30V VW-1

PIN ASSIGNMENT:



P/N	L(mm)	tolerance
AK672/2-1-R	1000	±30
AK672/2-2-R	2000	±50
AK672/2-3-R	3000	±50
AK672/2-5-R	5000	±50

Electrical test:
 1.100% short,open,miswire test
 2.Conduct resistance:5 Ohm(max)
 3.Insulation resistance:5Mohm(min)
 4.dielectric test:DC 300V

NO.	NAME	Q'TY	SPECIFICATION
⑧	PE BAG	1/5	CLEAR SIZE:360*380*0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS".
⑦	PE BAG	1	CLEAR SIZE:150*280*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC".
⑥	TIE	1	WHITE L=120mm
⑤	OUT JACKET	6g	BEIGE(IV-29#) PVC-40P (MOULD NO:WM-65)
④	OUT JACKET	6g	BEIGE(IV-29#) PVC-40P (MOULD NO:WM-40)
③	CABLE	1	BEIGE(IV-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm
②	CONN	1set	USB2.0 B MALE SHELL:NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 A MALE SHELL:NICKEL PIN G/F 4PCS TYPE INSULATOR COLOR:WHITE

RoHS compliant
 Unit:mm

Scale	FREE	Date	Name	Customer-No.
TOLERANCE		Drawn	11.02.2014	Joanna
X.X		Approved	11.02.2014	Joanna
X.XX				
X.XXX				
DIM	TOL			
X.°				
Angle	TOL	Id.	Modification	Date

ASSMANN WSW-No.
AK672/2-X-R

Drawing-No.
ASS 7066 CA

rev00

Replace Sheet