



① Cable White print
 AWM STYLE 2725 80°C 30V VW-1 28AWG/1P 24AWG/2C
 ---c AWM I/II A 80°C 30V FT1 USB CABLE

Electrical test:
 1. 100% short, open, miswire test
 ② 2. Conduct resistance:
 2 Ohm max. for cables of 2m below
 4 Ohm max. for cables of 3~5m
 3. Insulator resistance: 10Mohm min.
 4. Dielectric test: DC 300V

WSW P/N	Jacket color	Length(mm)
AK670/2-1-BLACK	Black	1000±30
AK670/2-2-BLACK	Black	2000±50
AK670/2-3-BLACK	Black	3000±50
AK670/2-5-BLACK	Black	5000±50



NO.	NAME.	Q'TY	SPECIFICATION	
⑤	PE Bag	1	Clear	Print black "MADE IN CHINA"+ "1PC"
④	TIE	1	Black	
③	Out Jacket	12g	Black	PVC-45P
②	Cable	1	USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm	Black
①	CONN	2	USB A Male Shell:Nickel Pin:G/F	Insulator color:White

RoHS compliant
 Unit: mm

Scale	Free					Date	Name	Customer-No.
TOLERANCE						Drawn	24.10.2014	Amy
						Approved	21.03.2016	Amy
		②	Correct conduct resistance	15.01.2019	Xavier			ASSMANN WSW-No. AK670/2-x-BLACK
DIM	TOL	①	Update the drawing	21.03.2016	Amy			Drawing-No. ASS 7243 CA
		①	Drawn	24.10.2014	Amy			rev01
Angle	TOL	Id.	Modification	Date	Name	Replace		Sheet