



RECOMMENDED PCB LAYOUT

NOTE:  
 MATERIAL:  
 HOUSING: THERMOPLASTIC (PBT+GF)  
 COLOR: BLACK/WHITE/BROWN/BEIGE ----  
 CONTACT: PHOSPHOR BRONZE  
 SHELL: BRASS  
 PLATING:  
 CONTACT: GOLD PLATING CORD: 5u"  
 SHELL: NICKEL PLATING  
 SPECIFICATION:  
 VOLTAGE RATING: 30V  
 CURRENT RATING: 1.5A  
 CONTACT RESISTANCE TERMINAL: 30mΩ MAX  
 DIELECTRIC WITHSTANDING VOLTAGE: 750V AC  
 INSULATION RESISTANCE: 1000MΩ MIN



<i>ITEM NO</i>	AU-Y1005-R (1.1 Version, 5μ" Gold) AU-Y1005-2-R (2.0 Version, 30μ" Gold)
<i>TITLE</i>	USB, for PCB mounting, Type A

**ASSMANN**  
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283  
Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED  
 © Copyright 2008 by Assmann Electronic Components  
 All International Rights Reserved