



AWHWxxG-0102-T-R
30u" of Gold

AWHWxxG-0202-T-R
Flash Gold

Current Rating: 3 Amps
 Insulator Resistance: 5000 Megohms min
 Dielectric Withstanding: AC 1000 V
 Operating Temperature: - 40° ~ +105° C
 Contact Material: Copper Alloy
 Insulator Material: Polyester, UL 94V-0
 Standard: PBT

Underplate: Nickel
 Contact Area: 1u"~30u" Selective Gold
 Solder Tails Area: 100u" Tin/Lead(Brighten Tin)or
 100u" Tin/Lead Free(Brighten Tin/Matte Tin)



Scale	1:1						Name	Item No.	
TOLERANCE					Drawn	10.19.11	Chappell	AWHWxxG-0202-T-R	
X.X	±0.40				Approved				Title Box Header, 2.54MM Pitch PCB Mount
X.XX	±0.25								Drawing No.
X.XXX	±0.15								rev00
Angle	±3°								Replace
								Sheet	
			Modification	Date	Name				

