



# P2




# P1

PIN OUT		
P1	568B Color	P2
1	White/Orange	1
2	Orange	2
3	White/Green	3
4	Blue	4
5	White/Blue	5
6	Green	6
7	White/Brown	7
8	Brown	8



1	2	3	4
BLU WH/BLU	ORG WH/ORG	GRN WH/GRN	BWN WH/BWN



150 cables per carton

**Material:**

- 4X2, 24AWG, twisted pair, 7\*0.19±0.15MM  
- OD: 5.2MM±0.30MM
- Insulation: HDPE-8380
- Jacket: PVC
- Contact Plug: UTP RJ45, 50µ"
- 568B Color wire standard
- Molded snaglass boot with strain relief
- Spot length on boot
- Connection 1:1



Scale	1:1							Name
TOLERANCE						Drawn	12.13.11	Chappell
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°							
		Modification		Date	Name			

Item No.	<b>DK-1511-007/BL</b>
Title	Cat 5e Patch Cord - Unshielded, Booted, UTP, 24AWG, Contact Plating 50µ" of Gold, Black, 7 Feet
Drawing No.	
Replace	rev00
Sheet	